

Multi-Axis Controller

V8 / VV8



GESSMANN®

The V8/VV8 is a robust joystick commonly used in electro-hydraulic applications. With many output options including voltage, amperage and switch contacts and many grip options the V8 / VV8 series is hugely customisable.

Technical data

Mechanical life V8	10 million operating cycles
Mechanical life VV8	20 million operating cycles
Operation temperature	-40°C to +85°C
Degree of protection	Up to IP54



		VV8	S5	P	T	-2RP	Example +3ZP	-B	-A05 P184	+A050 P184	E9012	-X
Basic unit												
VV8	Multi-Axis Controller 2-axis, reinforced version											
Control-handle extended												
	Standard 160 mm*											
S5	-20 mm											
S8	+20 mm											
	<i>*Only available in combination with a handle!</i>											
Gate												
P	Cross gate											
P X	Special gate											
Grip / Palm Grip												
T	Dead man											
Axis 1												
2	Contacts											
R	Friction brake											
P	Potentiometer											
Axis 2												
3	Contacts											
Z	Spring return											
P	Potentiometer											
Cover housing												
B	Cover housing											
Description axis 1 (direction 1-2)												
A050	Arrangement MSP21-0											
P184	Potentiometer T301 2 x 5 kOhm											
Description axis 2 (direction 3-4)												
A05	Arrangement MSP21											
P184	Potentiometer T301 2 x 5 kOhm											
Interface (description see on the following pages)												
E9012	Potentiometer output for proportional valve PVG32											
Special model												
X	Special / customer specified											

Technical details may vary based on configuration or application! Technical data subject to change without notice!

Combination possibilities with our grips

 p. 211	 p. 209	 p. 206	 p. 204	 p. 202	 p. 200	 p. 198	 p. 196	 p. 194
 p. 192	 p. 190	 p. 188	 p. 186	 p. 183	 p. 181	 p. 179	 p. 177	 p. 175
 p. 173	 p. 171	 p. 169	 p. 167	 p. 165	 p. 163			

		VV8	S5	P	T	-2 R P	+	3 Z P	-B	-	A05 P184	+	A050	P184	E9012	-	X
Basic unit																	
V81	1-axis																
V8	2-axis																
reinforced version																	
VV81	1-axis																
VV8	2-axis																
Control-handle extended																	
S5	-20 mm																
S8	+20 mm																
Gate																	
P	Cross gate																
P X	Special gate																
Grip/ Palm Grip																	
	Knob <i>(included in basic unit!)</i>																
M	Mechanical zero interlock																
MH	Mechanical zero interlock + signal contact																
T	Dead man																
H	Signal button																
D	Push button																
DV	Flush push button																
B...	Palm Grip B... <i>(see page Palm Grip 163)</i>																
Axis 1: direction 1-2																	
1	1 contact	Standard contact - arrangement see page 129															
2	2 contacts	e.g.															
3	3 contacts	A98				MS0				Zero position contact							
		A05				MS21				Direction contacts							
		A050				MS21-0				Direction contacts + zero position contact							
Z	Spring return																
R	Friction brake only available with a VV8!																

Technical details may vary based on configuration or application! Technical data subject to change without notice!

(P) Mounting options for potentiometer

P	Potentiometer	P181	T301 2 x 0,5 kOhm	I max. 1 mA
		P182	T301 2 x 1 kOhm	I max. 1 mA
		P183	T301 2 x 2 kOhm	I max. 1 mA
		P184	T301 2 x 5 kOhm	I max. 1 mA
		P185	T301 2 x 10 kOhm	I max. 1 mA
		More potentiometers on request!		
H	Hall-Potentiometer	E14811	0,5...2,5...4,5 V / 4,5 V...2,5...0,5	

VV8 S5 P T -2 R P + 3 Z P -B - A05 P184 + A050 P184 E9012 - X

Axis 2: direction 3-4 (not applied for V81/VV81)

1	1 contact	Standard contact - arrangement see page 129		
2	2 contacts	e.g.		
3	3 contacts	A98	MS0	Zero position contact
		A05	MS21	Direction contacts
		A050	MS21-0	Direction contacts + zero position contact
Z	Spring return			
R	Friction brake only available with a VV8!			
(P)	Mounting options for potentiometer			
P	Potentiometer	P181	T301 2 x 0,5 kOhm	I max. 1 mA
		P182	T301 2 x 1 kOhm	I max. 1 mA
		P183	T301 2 x 2 kOhm	I max. 1 mA
		P184	T301 2 x 5 kOhm	I max. 1 mA
		P185	T301 2 x 10 kOhm	I max. 1 mA
		More potentiometers on request!		
H	Hall-Potentiometer	E14811	0,5...2,5...4,5V/4,5V...2,5...0,5	

VV8 S5 P T -2 R P + 3 Z P -B - A05 P184 + A050 P184 E9012 - X

Cover housing

B Cover housing


Interface

	Potentiometer output	
E901	Potentiometer output for proportional valve PVG32	
	0,25...0,5...0,75 Us	
1	1 axis	
2	2 axis	
3	3 axis	
4	4 axis	


Special model

X Special / customer specified

T = Dead man's button
H = Signal button
M = Latch for mechanical zero interlock




Knob solid
D = Push button



Palm grip B3

for 3. Direction 11-12
for 4. Direction 13-14



Palm grip B25

